




Filters are used to protect valves, pumps, ejectors etc. from dust and other harmful particles.

In-line filters are designed to be serviced without removing the entire unit from the line. Simply remove the bowl and change the filter element. The transparent nylon bowl allows you to easily monitor the filter condition.

Filpro filters range in size from 1/4" to 1-1/2" NPT and are constructed from FDA approved 6/6 white nylon.



**Design Features**

- ◆ FDA approved 6/6 white nylon
- ◆ Buna N Gasket
- ◆ 10 micron polyethylene filter element
- ◆ Transparent nylon bowl shows condition of filter
- ◆ Pressure rating from full vacuum to 150 PSI
- ◆ Maximum temperature 120° F (49° C)




**Cleaning Requirements**

All elements can be easily cleaned or replaced without removing the entire strainer from the line by simply removing the bowl.



LOW PROFILE



REGULAR and LARGE

Part No.	A in. (mm)	B in. (mm)	C in. (mm)	D in. (mm)	Filter No.	Pipe Thread
<b>LOW PROFILE</b>						
FP.250 PIL	3.1	2.4	1.9	2.0	FP 25 RE	1/4" Male
FP.375 PIL	(78.7)	(61.0)	(48.3)	(50.8)		3/8" Male
<b>REGULAR</b>						
FP.375 PIL	3.7 (94.0)	5.4 (137.2)	3.0 (76.2)	4.8 (121.9)	FP 153 RE	3/8" Female
FP.500 PIL						1/2" Female
FP.750 PIL						3/4" Female
<b>LARGE</b>						
FP1.00 PIL	4.6 (116.8)	6.4 (162.6)	4.0 (101.6)	5.6 (175.3)	FP 224 RE	1" Female
FP1.25 PIL	5.2 (132.1)	6.4 (162.6)	4.0 (101.6)	6.9 (175.3)	FP 225 RE	1-1/4" Female
FP1.50 PIL	5.2 (132.1)	8.1 (205.9)	4.0 (101.6)	6.9 (175.3)	FP 252 RE	1-1/2" Female

**R.E. Morrison Equipment Inc.**

4161 Sladeview Crescent, Unit 5, Mississauga, Ontario L5L 5R3

www.remequip.com e-mail: info@remequip.com

(905) 828-6301 1-800-668-8736 Fax (905) 828-3674